



Pass and Seymour
15A 347V Specification Grade Decorator Switch, Light Almond
Part No. 2603LA

3-way, Back and Side-Wire, Decorator Switch, 15A, 120/277V



Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007539141
Country Of Origin	Mexico	Features	Decorator Style
Switch Type	Paddle	Number of Switches	1
Application Sector	Commercial, Industrial	Wall Plate Included	No
Standard	UL 20	Warranty Type	1-Year Limited Warranty

Type	Decorator, Switch		
Dimensions			
Product Width US	1.3 in	Product Depth US	1.06 in
Product Height US	4.2 in		
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17446		
Technical Information			
Operating Temperature Min	-4 °F	Load Rating	15 A @ 347 VAC
Connection Location	Back and Side	Terminal Accommodation	#14 AWG - #10 AWG
Operating Temperature Max	140 °F	Number of Gangs	1
Amperage	15 A	Number of Poles	Double Pole
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Operating Temperature	-20°-60°C, -4°-140°F
Wire Connection Type	Screw Terminals	Voltage	120 VAC, 277 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		