



Pass and Seymour  
15A 347V Specification Grade Decorator Switch, White  
Part No. 2603W

3-way, Back and Side-Wire, Decorator Switch, 15A, 120/277V



## Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see

## Specifications

### General Info

|                    |                        |                     |                         |
|--------------------|------------------------|---------------------|-------------------------|
| Product Line       | Pass & Seymour         | Color               | White                   |
| Finish             | Matte                  | UPC Number          | 785007539158            |
| Country Of Origin  | Mexico                 | Features            | Decorator Style         |
| Switch Type        | Paddle                 | Number of Switches  | 1                       |
| Application Sector | Commercial, Industrial | Wall Plate Included | No                      |
| Standard           | UL 20                  | Warranty Type       | 1-Year Limited Warranty |

|                                       |  |                        |                      |
|---------------------------------------|--|------------------------|----------------------|
| Type                                  | Decorator, Switch  |                        |                      |
| Dimensions                            |  |                        |                      |
| Product Width US                      | 1.3 in   | Product Depth US       | 1.06 in              |
| Product Height US                     | 4.2 in   |                        |                      |
| Listing Agencies / 3rd Party Agencies |  |                        |                      |
| CSA Listed                            | Yes  | cULus Listed           | Yes                  |
| CSA File Number                       | 17446  |                        |                      |
| Technical Information                 |  |                        |                      |
| Operating Temperature Min             | -4 °F  | Load Rating            | 15 A @ 347 VAC       |
| Connection Location                   | Back and Side  | Terminal Accommodation | #14 AWG - #10 AWG    |
| Operating Temperature Max             | 140 °F   | Number of Gangs        | 1                    |
| Amperage                              | 15 A   | Number of Poles        | Double Pole          |
| Requires Neutral Wire                 | No   | Indoor/Outdoor         | Indoor               |
| Mounting Type                         | Wall Box   | Operating Temperature  | -20°-60°C, -4°-140°F |
| Wire Connection Type                  | Screw Terminals  | Voltage                | 120 VAC, 277 VAC     |
| Load Type                             | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |                        |                      |