

3-way, Back and Side-Wire, Decorator Switch, 15A, 120/277V



Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 20		

Dimensions

Product Width US	1.3 in	Product Depth US	1.06 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

CSA File Number	17446
-----------------	-------

Technical Information

Contact Rating	15amp, 120/277vac	Amperage	15 A
----------------	-------------------	----------	------

Wattage	3 W	Voltage	120.0 V
---------	-----	---------	---------
