



Pass and Seymour
20A 120V/277V Specification Grade Double Pole Decorator Paddle Switch, Light Almond
Part No. 2622LA



Double-Pole, Back and Side-Wire, Decorator Switch, 20A, 120/277V.

Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007539462
Country Of Origin	Mexico	Features	Decorator Style
Switch Type	Paddle	Application Sector	Industrial
Standard	UL 20	Type	Switch

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140597
cULus Listed	Yes	CSA File Number	17446
Technical Information			
Operating Temperature Min	-4 °F	Operating Temperature Max	140 °F
Amperage	20 A	Wire Size	#14 - #10 AWG
Operating Temperature	-20°-60°C, -4°-140°F	Voltage	120/277 V