



Heavy-Duty Decorator Hospital Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body. **Rated 15 amperes**
- Heavy-duty compact design for easier installation and long lasting performance. **Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.**
- Impact-resistant nylon face. **Terminal compartments isolated from each other for positive conductor containment.**
- All devices fit standard #26 opening wall plate. **Tri-drive terminal and mounting screws.**
- Auto-ground clip assures positive ground. **Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact**

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor	Application Sector	Commercial
Standard	UL498, cUL CSA	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.833 in
------------------	----------	------------------	----------

Product Height US 2.635 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber 140596 cULus Listed Yes

Technical Information

Dielectric Strength Withstands 2000V minimum Connection Back and side wire

Number of Wires 3 Temperature Rating -40° - 60° C

Amperage 15 A Number of Poles Double Pole

Wire Size 14 - 10 AWG Indoor/Outdoor Indoor

Voltage 125.0 V Environmental Conditions Flammability: UL94 V2
