



Pass and Seymour
20A 120V Specification Grade 3-Way Illuminated Decorator Paddle Switch, White
Part No. 2626W

3-way, Back and Side-Wire, Illuminated Decorator Switch, 20A, 120 volts



Features & Benefits

Impact-resistant polycarb back body and frame.	Cushioned thermoplastic paddle assures smooth, quiet, long term operation.
Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.	Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.
Terminals made of high conductivity brass and serrated for maximum wire gripping.	Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.
Integral auto-ground clip for positive ground to metal boxes.	Tri-drive ground, terminal, and mounting screws.
All terminal screws backed out, ready-to-install.	For covering patents, see www.legrand.us/patents .

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007539851
Country Of Origin	Mexico	Features	Decorator Style
Switch Type	Paddle	Number of Switches	1
Application Sector	Commercial, Residential	Wall Plate Included	No

Standard	UL 20	Warranty Type	1-Year Limited Warranty
Type	Decorator, Switch		
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17446		
Technical Information			
Operating Temperature Min	-4 °F	Load Rating	20 A @ 120 VAC
Connection Location	Back and Side	Terminal Accommodation	#14 AWG - #10 AWG
Operating Temperature Max	140 °F	Number of Gangs	1
Amperage	20 A	Number of Poles	3-Way
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Operating Temperature	-20°-60°C, -4°-140°F
Wire Connection Type	Screw Terminals	Voltage	120 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		