



Pass and Seymour
20A 120V Specification Grade Single Pole Pilot Lighted Paddle Switch (Lighted When On), Light Almond
Part No. 2629LA

Single-Pole, Single Pilot Light, Side and Back Wire, Decorator Switch, 20A, 120 volts



Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007539943
Country Of Origin	Mexico	Features	Decorator Style
Switch Type	Paddle	Application Sector	Commercial, Residential
Standard	UL 20	Type	Decorator, Switch

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140597
cULus Listed	Yes	CSA File Number	17446

Technical Information

Operating Temperature Min	-4 °F	Contact Rating	20Amp, 120Vac
Operating Temperature Max	140 °F	Amperage	20 A
Wire Size	#14 - #10 AWG	Indoor/Outdoor	Indoor
Mounting Type	Box	Operating Temperature	-20°-60°C, -4°-140°F
Voltage	120.0 V		