



Heavy-Duty Decorator Spec Grade Duplex Receptacle Side Wire 20A 125V

Features & Benefits

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.	Rated 15 amperes
Heavy-duty compact design for easier installation and long lasting performance.	Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
Impact-resistant nylon face.	Terminal compartments isolated from each other for positive conductor containment.
Tri-drive terminal and mounting screws.	Auto-ground clip assures positive ground
For covering patents, see www.legrand.us/patents .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007785241
Country Of Origin	Mexico	Number of Receptacles	2
Application Sector	Commercial	Standard	UL 498, FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.833 in
Product Height US	2.635 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Amperage	20 A	Number of Poles	Double Pole
Wire Size	4 AWG	Indoor/Outdoor	Indoor