



Pass and Seymour  
Heavy Duty Decorator Spec Grade Single Receptacles, Back and Side Wire 15A 250V, Ivory  
Part No. 26661I



Heavy-Duty Decorator Spec Grade Single Receptacle Back and Side-Wire 15A 250V

## Features & Benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- Heavy-duty compact design for easier installation and long lasting performance.
- Impact-resistant nylon face.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- Tri-drive terminal and mounting screws.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Terminal compartments isolated from each other for positive conductor containment.
- All devices fit standard #26 opening wall plate.
- Auto-ground clip assures positive ground.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 498		

---

## Dimensions

---

Product Width US	1.322 in	Product Depth US	1.188 in
Product Length US	2.635 in		

---

## Listing Agencies / 3rd Party Agencies

---

cUL ListingNumber	140596	cUL Listed	Yes
-------------------	--------	------------	-----

---

## Technical Information

---

Phase	3	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	250.0 V

---