



Heavy-Duty Decorator Spec Grade Single Receptacle Back and Side-Wire 20A 250V



Features & Benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
 - Heavy-duty compact design for easier installation and long lasting performance.
 - Impact-resistant nylon face.
 - Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
 - Tri-drive terminal and mounting screws.
 - For covering patents, see www.legrand.us/patents.
 - Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
 - Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
- One-piece, brass, triple-wipe power contacts for lasting retention.
 - Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
 - Terminal compartments isolated from each other for positive conductor containment.
 - All devices fit standard #26 opening wall plate.
 - Auto-ground clip assures positive ground.
 - For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 498		

Dimensions

Product Width US	1.322 in	Product Depth US	1.188 in
Product Length US	2.635 in		

Listing Agencies / 3rd Party Agencies

cUL ListingNumber	140596	cUL Listed	Yes
-------------------	--------	------------	-----

Technical Information

Phase	3	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	250.0 V
