



Locking Dust-Tight Rubber Connector, 20amp 277volt, NEMA Configuration L7-20.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather Two Screw cable clamp secures wire and provides superior strain relief

Quick lead assembly screws aid in a fast installation

Industrial strength, brass blades and contacts resist heat rise while providing excellent conductivity

Keyed body and cover for easy assembly and alignment

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Yellow	UPC Number	785007033038
Country Of Origin	United States	Product Line	Pass & Seymour
Standard	UL Listed, CSA Listed		

Technical Information

Number of Poles	Double Pole	Voltage	277 V
Phase	Single	Wire Size	14 AWG min - 10 AWG max
Number of Wires	3	Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed materials are UV stabilized