



Pass and Seymour
Rubber Dust-Tight NEMA L15-20 Locking Connector, 20A 250V, Yellow
Part No. 2775



Locking Dust-Tight Rubber Connector, 20amp 3250, NEMA Configuration L15-20.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather

Quick lead assembly screws aid in a fast installation

Keyed body and cover for easy assembly and alignment

Two Screw cable clamp secures wire and provides superior strain relief

Industrial strength, brass blades and contacts resist heat rise while providing excellent conductivity

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033663	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

Dimensions

Product Width US	2.14 in	Product Length US	4.06 in
------------------	---------	-------------------	---------

Technical Information

Phase	Three	Number of Wires	4
Amperage	20 A	Number of Poles	3-Way

Wire Size	14 - 10 AWG	Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized
-----------	-------------	--------------------------	--
