



Locking Dust-Tight Rubber Plug, 30amp 3480, NEMA Configuration L16-30

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather

Quick lead assembly screws aid in a fast installation

Keyed body and cover for easy assembly and alignment

Two Screw cable clamp secures wire and provides superior strain relief

Industrial strength, brass blades and contacts resist heat rise while providing excellent conductivity

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------|-----------------------|-------------------|---------------|
| Product Line | Pass & Seymour | Color | Yellow |
| UPC Number | 785007033427 | Country Of Origin | United States |
| Standard | UL Listed, CSA Listed | | |

Dimensions

| | | | |
|------------------|--------|-------------------|----------|
| Product Width US | 2.3 in | Product Length US | 2.963 in |
|------------------|--------|-------------------|----------|

Technical Information

| | | | |
|----------|-------|-----------------|-------|
| Phase | Three | Number of Wires | 4 |
| Amperage | 30 A | Number of Poles | 3-Way |

| | | | |
|-----------|------------|--------------------------|---|
| Wire Size | 12 - 6 AWG | Environmental Conditions | Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized |
|-----------|------------|--------------------------|---|
