



Pass and Seymour  
**Watertight NEMA 4X/6P Locking Plug, Yellow**  
Part No. 28W47



Locking Watertight Plug, 30amp 125volt, NEMA Configuration L5-30, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P and IP67 rated.

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color coded sealing bushings provided for large range of cord diameters

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Standard	UL Listed, CSA Listed

### Dimensions

Product Height US	2.35 in	Product Length US	3.1 in
-------------------	---------	-------------------	--------

### Technical Information

Phase	Single	Number of Wires	3
Amperage	30 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	125.0 V

---

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65,  
66, 67 (Plug & Connector only) Flammability  
UL94V0 (boxes & wiring device interiors) Operating  
Temperature -40°C (without impact) to +60°C  
continuous UV resistance All exposed material s  
are UV stabilized

---