



Pass and Seymour
28W74 Watertight NEMA 4X/6P Locking Plug, Yellow
Part No. 28W74



Locking Watertight Plug, 30amp 125/250volt, NEMA Configuration L14-30, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P and IP67 rated.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat , and weather.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color coded sealing bushings provided for large range of cord diameters

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

Specifications

General Info

| | | | |
|-------------------|----------------|----------|-----------------------|
| Product Line | Pass & Seymour | Color | Yellow |
| Country Of Origin | United States | Standard | UL Listed, CSA Listed |

Dimensions

| | | | |
|-------------------|---------|-------------------|--------|
| Product Height US | 2.35 in | Product Length US | 3.1 in |
|-------------------|---------|-------------------|--------|

Technical Information

| | | | |
|-----------|------------|-----------------|---------|
| Phase | Single | Number of Wires | 4 |
| Amperage | 30 A | Number of Poles | 3-Way |
| Wire Size | 12 - 6 AWG | Voltage | 125.0 V |

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65,
66, 67 (Plug & Connector only) Flammability
UL94V0 (boxes & wiring device interiors) Operating
Temperature -40°C (without impact) to +60°C
continuous UV resistance All exposed material s
are UV stabilized
