



## Pass and Seymour 28W75 Watertight NEMA 4X/6P Locking Plug, Yellow Part No. 28W75



Locking Watertight Plug, 30amp 3 250 volt, NEMA Configuration L15-30, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P & IP67 rated.

### Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Devices resist high-pressure hose down of 1,500 psi.

Color coded sealing bushings provided for large range of cord diameters

Large ribs on body for a superior grip when mating.

### Specifications

#### General Info

Color	Yellow	UPC Number	785007033267
Country Of Origin	United States	Product Line	Pass & Seymour
Standard	UL Listed, CSA Listed		

#### Technical Information

Number of Poles	3-Way	Voltage	250 V
Phase	Three	Wire Size	12 AWG min - 6 AWG max
Number of Wires	4	Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed materials are UV stabilized