



Pass and Seymour  
Turnlok® 30A, 3° 480V Watertight Plug, NEMA 4X/6P, Black  
Part No. 28W76BK



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour watertight plugs and connectors feature multiple seals to ensure protection against the environment. Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Multi-point sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color-coded sealing bushings provided for large range of cord diameters

For Covering Patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Devices resist high-pressure hosedown of 1,500 psi.

Large ribs on body for a superior grip when mating.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007040920	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

### Dimensions

Product Width US	1.85 in	Product Depth US	3.1 in
Product Height US	1.85 in		

### Technical Information

Phase	Three	Number of Wires	4
-------	-------	-----------------	---

Amperage	30 A	Number of Poles	3-Way
Wire Size	12 - 6 AWG	Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized