



Pass and Seymour 29W09 Watertight NEMA 4X/6P Locking Connector Part No. 29W09



Watertight Connector, 30amp 3Y 120/208V, Non-NEMA Configuration, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Devices resist high-pressure hose down of 1,500 psi.

Color coded sealing bushings provided for large range of cord diameters

Large ribs on body for a superior grip when mating.

Specifications

General Info

Color	Yellow	UPC Number	785007033311
Country Of Origin	United States	Product Line	Pass & Seymour
Standard	UL Listed, CSA Listed		

Technical Information

Number of Poles	3-Way	Voltage	120 V
Phase	Single	Wire Size	14 AWG min - 10 AWG max
Number of Wires	3	Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed materials are UV stabilized