



Pass and Seymour
Trademaster® 15A 125V Self-Grounding Duplex Receptacle, White
Part No. 3232SW



15A/125A Trademaster® Duplex Receptacle

Features & Benefits

Quality Materials, durability, and time-tested design

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Residential, Self-Grounding
Application Sector	Residential	Standard	UL498, CSA C22.2 No. 42
Type	Outlet		

Dimensions

Product Width US	1.32 in	Product Depth US	0.96 in
Product Height US	3.31 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Temperature Rating -30° - 60° C Amperage 15 A

Number of Poles Double Pole Wire Size 14 - 12 AWG

Indoor/Outdoor Indoor Voltage 125.0 V
