



Pass and Seymour  
Trademaster® 20A 125V Tamper-Resistant Duplex Receptacle, Black  
Part No. 3232TR20SBK



Easily add the power every home needs with Legrand's 20A/125V Trademaster® Tamper-Resistant, Self-Grounding, Duplex Receptacle. This 20-amp receptacle offers a self-grounding feature that makes these receptacles ideal for residential and multi-dwelling units. Additionally, the receptacle has black "invisi-shutters" that are not visible by end users but help to prevent improper insertion of foreign objects to comply with NEC Article 406.12.

## Features & Benefits

- Ideal for Residential Applications & Multi-Dwelling units where 20A devices are required
- Meets National Electric Code Tamper-Resistant requirements per Article 406.12
- Black "Invisi-Shutters" disappear for an invisible effect
- Side Wire Only accepts #12-#14 AWG
- Auto-Ground Clip assures a positive ground connection is made

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Finish	Glossy	UPC Number	785007445657
Country Of Origin	China	Receptacle Type	Straight Blade
Number of Receptacles	2	Features	Self-Grounding
Outlet Type	Self-Grounding, Tamper-Resistant	Application Sector	Commercial, Residential
Standard	RoHs, UL (UL498, E140596), cULus (UL498, E140596), CSA (C22.2 No. 42)	Warranty Type	1-Year Limited Warranty
Type	Decorator, Duplex, Outlet		

### Dimensions

Product Width US	1.42 in	Product Weight US	0.122 lb
Product Depth US	1.03 in	Product Height US	4.2 in

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	UL498
cULus Listed	Yes	CSA File Number	C22.2 No. 42

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Seismic Tested	No	Is Tamper-Resistant	Yes
Connection	Side Wire Only	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Is Weather Resistant	No
Indoor/Outdoor	Indoor	Mounting Type	Box
Environmental Conditions	98% (relative humidity, non-condensing)		