



Pass and Seymour  
Trademaster® 15A 125V Tamper-Resistant Weather-Resistant Duplex Receptacle, Brown  
Part No. 3232TRWR



15A/125A Weather-Resistant Duplex Receptacle,

## Features & Benefits

Quality Materials, durability, and time-tested design

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Wire Size: #12 - #14 AWG, Solid wire

## Specifications

### General Info

|                       |                |                   |   |
|-----------------------|----------------|-------------------|---|
| Product Line          | Pass & Seymour | Color             | Brown   |
| Finish                | Matte          | Country Of Origin | Mexico  |
| Number of Receptacles | 2              | Outlet Type       | Commercial, Outdoor, Residential, Tamper-Resistant, Weather-Resistant |
| Application Sector    | Residential    | Standard          | cULus UL498, CSA C22.2 No. 42   |
| Type                  | Outlet         |                   |   |

### Dimensions

|                   |         |                  |        |
|-------------------|---------|------------------|--------|
| Product Width US  | 1.32 in | Product Depth US | 1.0 in |
| Product Height US | 3.31 in |                  |        |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

## Additional Information

---

Product Environmental Profile      Yes

---

## Technical Information

---

Temperature Rating                      -30° - 60° C                      Amperage                      15 A

---

Number of Poles                      Double Pole                      Wire Size                      14 - 12 AWG

---

Indoor/Outdoor                      Outdoor                      Voltage                      125.0 V

---