



Pass and Seymour

30 Amp Non-NEMA 3 Wire - Single Receptacle, Grounding
Part No. 3330G

Receptacle Single 30amp 125/250volt Turnlok



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

UPC Number	785007333077	Country Of Origin	Mexico
------------	--------------	-------------------	--------

Product Line	Pass & Seymour	Application Sector	Industrial
--------------	----------------	--------------------	------------

Standard	UL Listed
----------	-----------

Technical Information

Number of Poles	Double Pole	Voltage	125 V
-----------------	-------------	---------	-------

Phase	3	Number of Wires	3
-------	---	-----------------	---