

Receptacle Single 30A 125/250V Turnlok®



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL Listed

Dimensions

Product Width US	1.437 in	Product Depth US	0.97 in
Product Height US	2.375 in		

Technical Information

Phase	3	Number of Wires	3
-------	---	-----------------	---

Amperage

30 A

Number of Poles

Double Pole

Voltage

125.0 V
