



Wiremold  
Discontinued - Power Commander PDU/120V/30A/single phase/36 pcs 5-20R O/L  
Part No. 3A86B2-1



Two 15A resettable circuit breakers. Thirty-six 20A outlets with T-slots, gray housing.  
12' (3.6m) cord. Length 70" (1.8m).

Specifications

General Info

|                       |                                       |                    |              |
|-----------------------|---------------------------------------|--------------------|--------------|
| Product Line          | Wiremold                              | UPC Number         | 786776034387 |
| Country Of Origin     | Mexico                                | Receptacle Type    | Simplex      |
| Number of Receptacles | 36                                    | Application Sector | Commercial   |
| Standard              | cULus Listed: File E173292 Guide NWGQ | Type               | PIOC         |

Listing Agencies / 3rd Party Agencies

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E173292 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Buy American Act Compliance

|       |     |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

Additional Information

|                 |     |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

Technical Information

|       |        |                  |       |
|-------|--------|------------------|-------|
| Phase | Single | Frequency Rating | 60 Hz |
|-------|--------|------------------|-------|

|                          |                                                                 |                |          |
|--------------------------|-----------------------------------------------------------------|----------------|----------|
| Amperage                 | 20 A                                                            | Enclosure Type | Aluminum |
| Mounting Type            | Drop-In Clip, Swivel Bracket, Z Bracket, L Bracket, Spring Clip | Voltage        | 100.0 V  |
| Environmental Conditions | Dry interior locations                                          |                |          |