



Accepts front-loading TracJack modules and includes two snap-in label fields. Available in 1, 2, 3, 4 gangs. In addition to the Plastic TracJack Faceplate, Legrand offers a full range of TracJack faceplates in stainless steel, with a variety of port capacities to match your workstation applications. All TracJack plates offer recessed label fields.

Features & Benefits

- Low profile design: Blends with most environments.
- Recessed label fields: Supports TIA/EIA 606 standard.
- Easily accepts snap-in TracJacks: Easily field configured.
- Front-load module approach: Improves access for future work.
- Textured finish: Hides future scuffs.

Specifications

General Info

| | | | |
|--------------------|--------------------------------|-----------------|----------------------------|
| Product Line | Ortronics | Color | Fog White |
| Finish | Smooth | UPC Number | 662875279228 |
| Country Of Origin | Taiwan, Province Of China | Features | Front Loading, Label Field |
| Included | Label Field, Mounting Hardware | Wall Plate Type | Networking |
| Application Sector | Commercial | Standard | UL Standard |
| Warranty Type | 5-Year | Type | Workstation |

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|---------------------------|-------------|---------------------------|-----------|
| Operating Temperature Min | -10 °C | Compatibility | TracJack |
| Number of Ports | 8 | Operating Temperature Max | 60 °C |
| Number of Gangs | 2 | Indoor/Outdoor | Indoor |
| Mounting Type | Box Mounted | Operating Temperature | -10°-60°C |
| Orientation | Vertical | | |