



Ortronics

HDJ 6 PORT DOUBLE GANG FACEPLATE, WITH LABEL FIELD, CLOUD WHITE

Part No. 403HDJ26-88



HDJ faceplates are available in 1, 2, 3, 4 & 6 port in a single gang and 6 & 12 port in a double gang. HDJ faceplates support rear load installation of HDJ copper series jacks and HDFM fiber modules. All faceplates include label fields.

Features & Benefits

Low profile design: Blends with most environments	Recessed label fields: Supports TIA/EIA 606 standard.
Accepts snap-in High Density Jacks (HDJ): Easily field configured.	Textured finish: Hides scuffs
Oval mounting holes: Assists proper alignment.	Compatible with all HDJ adapters and connectors, including shielded

Specifications

General Info

Product Line	Ortronics	Color	Cloud White
Finish	Textured	UPC Number	662875834915
Country Of Origin	Taiwan, Province Of China	Wall Plate Type	Networking
Application Sector	Commercial	Standard	UL Standard
Warranty Type	5-Year	Type	Workstation

Dimensions

Product Width US	2.76 in	Product Depth US	0.31 in
Product Height US	4.53 in		

Additional Information

Product Environmental Profile Yes

Technical Information

Operating Temperature Min	-10 °C	Compatibility	HDJ
Number of Ports	6	Operating Temperature Max	60 °C
Number of Gangs	2	Indoor/Outdoor	Indoor
Mounting Type	Box Mounted	Operating Temperature	-10°-60°C
Orientation	Vertical		