



Ortronics
TracJack Stainless Steel Wall Phone Plate with Mounting Studs
Part No. 403STJ1WP



Legrand Registered offers TracJack Registered mountings in both the 106-Type duplex footprint or the Stylistics Registered rectangular (GFCI) footprint, with a variety of port capacities to match your workstation applications. These two footprints are common to Wiremold Registered and many other industry standard raceway, furniture, pedestals and floor boxes. Legrand also offers plastic cover plates with recessed label fields and slotted screw holes to adjust alignment. All parts are ruggedly constructed from high impact thermo-plastic 94V-0 rated to ensure long life.

Features & Benefits

Manufactured from 304 stainless steel

Corrosion resistant

Non-magnetic material

Specifications

General Info

Product Line	Ortronics	Color	Fog White
Finish	Brushed	UPC Number	662875629634
Country Of Origin	Taiwan, Province Of China	Material	Stainless Steel
Features	Front Loading	Wall Plate Type	Networking
Application Sector	Commercial	Standard	UL Standard
Warranty Type	5-Year	Type	Wall Plate

Dimensions

Product Width US	2.74 in	Product Depth US	0.24 in
Product Height US	4.5 in		

Additional Information

Product Environmental Profile Yes

Technical Information

Operating Temperature Min	-10 °C	Compatibility	TracJack
---------------------------	--------	---------------	----------

Number of Ports	1	Operating Temperature Max	60 °C
-----------------	---	---------------------------	-------

Number of Gangs	1	Indoor/Outdoor	Indoor
-----------------	---	----------------	--------

Mounting Type	Exposed Screws	Operating Temperature	-10°-60°C
---------------	----------------	-----------------------	-----------

Orientation	Vertical
-------------	----------
