



TracJack 106-Type Plastic Duplex Frame accepts two front-loading TracJack modules. It is compatible with many cable delivery systems that can house electrical duplex outlets

Features & Benefits

Matches duplex electrical outlet footprint: Supports use with electrical delivery system.

Field configurable with TracJacks: Design or site flexibility for new or retrofit

Supports TracJack footprint: Broad offering of connector options.

Front load and access: Connector access without removing plate.

Choice of four colors: Compatible with many environments.

Specifications

General Info

| | | | |
|--------------------|---------------------------|-----------------|------------------|
| Product Line | Ortronics | Color | Electrical Ivory |
| Finish | Smooth | UPC Number | 662875344308 |
| Country Of Origin | Taiwan, Province Of China | Wall Plate Type | Networking |
| Application Sector | Commercial | Standard | UL Standard |
| Warranty Type | 5-Year | Type | Workstation |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.75 in | Product Depth US | 0.45 in |
| Product Height US | 4.09 in | | |

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|---------------------------|----------------|---------------------------|-----------|
| Operating Temperature Min | -10 °C | Compatibility | TracJack |
| Number of Ports | 2 | Operating Temperature Max | 60 °C |
| Number of Gangs | 1 | Indoor/Outdoor | Indoor |
| Mounting Type | Exposed Screws | Operating Temperature | -10°-60°C |
| Orientation | Vertical | | |
