



Stainless Steel Cover With Bubble, Round Mat, 4 Screw Box Mounting

Features & Benefits

Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).	Plate is Type 302 Stainless Steel for corrosion resistance.
Transparent silicone rubber mat seals plate and opening from contamination.	Switch easily actuated through flexible silicone bubble.
Silicone mat maintains pliability from -100 degrees F to +250 degrees F.	Mat is resistant to grease, water, steam, detergents, aging, and ozone.

Specifications

General Info

Product Line	Pass & Seymour	Color	Stainless Steel
Finish	Metallic	UPC Number	785007451597
Country Of Origin	United States	Features	Weatherproof
Wall Plate Type	Custom	Application Sector	Commercial, Industrial
Standard	UL Listed	Warranty Type	1-Year Limited Warranty
Type	Weatherproof Cover		

Technical Information

Indoor/Outdoor	Outdoor	Mounting Type	Box Mounted
Number of Outlets	1		