



This Dell® 462-3619 compatible SFP transceiver provides 1000Base-TX throughput up to 100m over a copper connection using a RJ-45 connector. It is guaranteed to be 100% compatible with the equivalent Dell® transceiver. Our TX transceiver modules support 10/100/1000Mbs auto-negotiation and can be configured to fit your needs. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. It is built to meet or exceed the specifications of Dell®, as well as to comply with MSA (Multi-Source Agreement) standards to ensure seamless network integration. All Legrand transceivers are Trade Agreements Act (TAA) compliant.

Features & Benefits

Transceiver type TX allows for connections up to 100m	SFP (mini-GBIC) transceiver module
RJ45 port designed for use with a copper patch cable	

Specifications

General Info

Product Line	Legrand	Color	Silver
UPC Number	757120669548	Country Of Origin	United States
Application Sector	Commercial/Industrial		

Buy American Act Compliance

TAA Compliant	Yes
---------------	-----

Additional Information

RoHS Conformant	Yes	Product Has Potential to Contribute to LEED	Yes
-----------------	-----	---	-----