

Turnlok® Flanged Outlet 3-Wire 15A 125V Grounding



Features & Benefits

Interior components constructed of high-grade brass material for physical and electrical integrity. High-impact thermoplastic housing withstands on-the-job abuse.

Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498

Dimensions

Product Width US	2.562 in	Product Depth US	1.374 in
------------------	----------	------------------	----------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
cUL Listed	Yes		

Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 10 AWG

Voltage

125.0 V
