

Turnlok® Receptacle Duplex 15A 277V



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007475005
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498		

Dimensions

Product Width US	1.322 in	Product Depth US	1.199 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

CSA File Number	16063
-----------------	-------

Technical Information

Number of Wires	3	Amperage	15 A
-----------------	---	----------	------

Number of Poles	Double Pole	Wire Size	18 - 10 AWG
-----------------	-------------	-----------	-------------

Voltage	277.0 V
---------	---------