

Receptacle Duplex Combination



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Commercial	Standard	UL 498

Dimensions

Product Width US	1.5 in	Product Depth US	1.199 in
Product Height US	3.28 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	NO
------------	-----	-----------------	----

Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 10 AWG
Voltage	125.0 V		
