



Wiremold
CabinetMate Plug-In Outlet Center Unit / 120V/20A / 48" long / 10 O/L / 6' cord / Computer Grade Surge
 Part No. 4810BCS20R



Ten 20A outlets with t-slots. 6' (1.8m) cord. Length 48" (1.2m). Computer grade surge protection, 20 Amps.

Features & Benefits

Ten outlets. 15' (4.6m) cord. Length 48" (1.2m). 15A resettable circuit breaker. Computer grade surge protection, 15 Amps.

Specifications

General Info

Product Line	Wiremold	Color	Black, Gray
UPC Number	786776052671	Country Of Origin	Mexico
Material	Aluminum	Product Series	CabinetMate
Number of Receptacles	10	Features	Surge Protection
Application Sector	Commercial, Residential	Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	PIOC

Dimensions

Product Width US	48.0 in	Product Weight US	4.0 lb
Product Height US	1.13 in	Product Length US	1.5 in
Receptacle Spacing	4 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Phase	Single Stage	Cord Length	6 ft
-------	--------------	-------------	------

Connection	Cord-ended	Class	75
------------	------------	-------	----

Amperage	20 A	Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]
----------	------	----------------------	---

Response Time	<1 ns	Wiring Method	Cord-ended
---------------	-------	---------------	------------

NEMA Configuration Code	5-20P, 5-20R	Mounting Type	Spring Clip
-------------------------	--------------	---------------	-------------

Mounting	Yes	Type of Indicators	Light
----------	-----	--------------------	-------

Voltage	120.0 V
---------	---------
