



Wiremold

CabinetMate Plug-In Outlet Center Unit / 120V/15A / 48" long / 10 O/L / 15' cord / Computer Grade Surge

Part No. 4810BDS



Ten outlets. 15' (4.6m) cord. Length 48" (1.2m). 15A resettable circuit breaker. Computer grade surge protection, 15 Amps.

Features & Benefits

Ten outlets. 15' (4.6m) cord. Length 48" (1.2m). 15A resettable circuit breaker. Computer grade surge protection, 15 Amps.

Specifications

General Info

| | | | |
|-------------------|---|--------------------|------------------------|
| Product Line | Wiremold | UPC Number | 786776117998 |
| Country Of Origin | Mexico | Application Sector | Residential/Commercial |
| Standard | cULus Listed: File E66421 Guide XYBS XUHT VZCA | Type | PIOC |

Dimensions

| | | | |
|-------------------|---------|-------------------|---------|
| Product Width US | 48.0 in | Product Height US | 1.13 in |
| Product Length US | 1.5 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E66421 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Buy American Act Compliance

| | |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

Additional Information

| | |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

Technical Information

| | | | |
|-------|--------------|------------------|----------|
| Phase | Single Stage | Frequency Rating | +35dB Hz |
|-------|--------------|------------------|----------|

| | | | |
|------------|------------|-------|----|
| Connection | Cord-ended | Class | 75 |
|------------|------------|-------|----|

| | | | |
|----------|------|----------------------|--|
| Amperage | 15 A | Short Circuit Rating | 36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G] |
|----------|------|----------------------|--|

| | | | |
|---------------|-------|---------------|-------------|
| Response Time | <1 ns | Mounting Type | Spring Clip |
|---------------|-------|---------------|-------------|

| | | | |
|----------|-----|--------------------|-------|
| Mounting | Yes | Type of Indicators | Light |
|----------|-----|--------------------|-------|

| | |
|---------|---------|
| Voltage | 600.0 V |
|---------|---------|
