



Wiremold  
**4IN PREWIRED FLUSH SYLE DUP CR SN**  
 Part No. 4ATP2CRSN



Designed for retrofit and new construction, Evolution Series 4" Recessed Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. With 2 Gangs of capacity, you will be able to configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel, and multiple powder-coated finishes designed to match any space. Evolution Series 4" Poke-Thru devices are the perfect fit for kiosks, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture.

## Features & Benefits

**Prewired assembly:** Save on labor with a completely assembled, prewired poke-thru with every power receptacle already installed.

**Recessed devices:** All power devices are recessed below floor level, providing maximum protection and device longevity.

**Step-on-it installation:** Quick and easy installation without the need for additional fasteners or a second installer.

**Unique cover design:** The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe

**Multiple finishes:** Evolution Series Poke-Thru Devices are available in multiple finishes, (BK) black, (GY) gray, (BZ) bronze, (AL) aluminum, (AA) brushed aluminum, (SB) satin brass, and (SN) satin nickel to seamlessly match your environment.

**Surface style cover assemblies:** A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.

**2 hour fire rating:** Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 2 hours.

**Meets ADA accessibility guidelines:** Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.

**UL Listed and UL fire classified to U.S. and Canadian safety standards:** UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

## Specifications

### General Info

Product Line	Wiremold	Color	Nickel
UPC Number	786564105152	Country Of Origin	United States
Receptacle Type	Straight Blade	Number of Receptacles	1

---

Number of Knockouts	10	Application Sector	Commercial
Standard	UL	Type	Poke-Thru

---

#### Dimensions

---

Cubic Capacity	25 cu in	Core Hole Size	4 in
----------------	----------	----------------	------

---

#### Additional Information

---

Product Has Potential to Contribute to LEED Yes

---

#### Technical Information

---

Floor Type	Concrete	Is Tamper-Resistant	No
Fire Rating	2 hr	Amperage	20 A
Current Rating	20 A	NEMA Configuration Code	5-20R
Number of Outlets	2	Voltage	125.0 V

---