



Wiremold
Discontinued - Power Commander PDU/120V/40A/split-phase (2 x 20A)/24 pcs 5-20R O/L
Part No. 4B44B2-2



Two circuits with two 20A resettable circuit breakers. Twenty-four 20A outlets with T-slots, black housing. 12' (3.6m) cord. Length 48" (1.3m).

Features & Benefits

Two circuits with two 20A resettable circuit breakers. Twenty-four 20A outlets with T-slots, black housing. 12' (3.6m) cord. Length 48" (1.3m).

Specifications

General Info

Product Line	Wiremold	UPC Number	786776061109
Country Of Origin	Mexico	Receptacle Type	Simplex
Number of Receptacles	24	Application Sector	Commercial
Standard	cULus Listed: File E173292, Guide NWGQ	Type	PIOC

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E173292	cULus Listed	Yes
---------------------	---------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Phase	Single	Frequency Rating	60 Hz
Amperage	20 A	Enclosure Type	Aluminum
Mounting Type	Spring Clip, Drop-In Clip, Swivel Bracket, L Bracket, Z Bracket	Voltage	120.0 V
Environmental Conditions	Dry interior locations		
