



Wiremold  
Discontinued - Power Commander PDU/120V/40A/split-phase (2 x 20A)/24 pcs 5-20R O/L  
Part No. 4B44B2-2



Two circuits with two 20A resettable circuit breakers. Twenty-four 20A outlets with T-slots, black housing. 12' (3.6m) cord. Length 48" (1.3m).

## Features & Benefits

Two circuits with two 20A resettable circuit breakers. Twenty-four 20A outlets with T-slots, black housing. 12' (3.6m) cord. Length 48" (1.3m).

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776061109
Country Of Origin	Mexico	Receptacle Type	Simplex
Number of Receptacles	24	Application Sector	Commercial
Standard	cULus Listed: File E173292, Guide NWGQ	Type	PIOC

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E173292	cULus Listed	Yes
---------------------	---------	--------------	-----

### Additional Information

RoHS Compliant	Yes
----------------	-----

### Technical Information

Phase	Single	Amperage	20 A
-------	--------	----------	------

Enclosure Type	Aluminum	Mounting Type	Spring Clip, Drop-In Clip, Swivel Bracket, L Bracket, Z Bracket
Voltage	120.0 V	Environmental Conditions	Dry interior locations