



Pass and Seymour
15A 125V Heavy Duty Spec-Grade Single Receptacle, Side Wire, White
Part No. 5251W



Heavy-Duty Spec Grade Single Receptacle Side, Wire 15A 125V

Features & Benefits

Auto-ground clip assures positive ground.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.

One-piece brass triple-wire power contacts for lasting retention.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007525151
Country Of Origin	Mexico	Number of Receptacles	1
Application Sector	Commercial	Standard	UL 498
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.38 in	Product Depth US	1.08 in
------------------	---------	------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage	15 A	Number of Poles	Double Pole
Wire Size	4 AWG	Indoor/Outdoor	Indoor