



Short Strap Spec Grade Single Receptacle, Side Wire, 15A 125V

Features & Benefits

Auto-ground clip assures positive ground.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

One-piece brass triple-wipe power contacts for lasting retention.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Backed-out tri-drive steel terminal screws.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Number of Receptacles	1
Outlet Type	Commercial, Indoor	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42	Type	Outlet

Dimensions

Product Depth US	1.0 in	Product Height US	1.49 in
------------------	--------	-------------------	---------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
---------------------	--------------------------	------------	--------------------

Number of Wires	3	Temperature Rating	-40° - 60° C
-----------------	---	--------------------	--------------

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2
---------	---------	--------------------------	-----------------------
