



Pass and Seymour
Flanged Inlet, Gray
Part No. 5278SS



Straight Blade 2-Pole 3-Wire 15A 125V Flanged Inlet

Features & Benefits

All thermoplastic construction, provides excellent impact and chemical resistance.

NEMA configuration molded on flange, easy field identification.

Available in Gray or Black.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Standard	UL 498
Type	Straight Blade		

Dimensions

Product Width US	2.562 in	Product Depth US	1.655 in
------------------	----------	------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection	Wire Grounding	Number of Wires	3
------------	----------------	-----------------	---

Amperage	15 A	Number of Poles	Double Pole
Wire Size	4	Voltage	125.0 V
