



Pass and Seymour  
20A 125V Heavy Duty Spec-Grade Single Receptacle, Side Wire, Light Almond  
Part No. 5351LA



Heavy-Duty Spec Grade Single Receptacle Side Wire 20A 125V

## Features & Benefits

Auto-ground clip assures positive ground.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

One-piece brass triple-wire power contacts for lasting retention.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Factory-broken split-circuit tab allows for 50% plug load control to be achieved in one duplex receptacle.

Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate side wire capability.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007535136
Country Of Origin	Mexico	Number of Receptacles	1
Application Sector	Commercial	Standard	UL 498
Warranty Type	1-Year Limited Warranty	Type	Outlet

### Dimensions

Product Width US	1.38 in	Product Depth US	1.08 in
------------------	---------	------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection	Wire Ground	Number of Wires	3
------------	-------------	-----------------	---

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	4 AWG	Indoor/Outdoor	Indoor
-----------	-------	----------------	--------