



Pass and Seymour  
20A 125V Short Strap Spec Grade Single Receptacle, Side Wire, White  
Part No. 5358W



Short Strap Spec Grade Single Receptacle, Side Wire, 20A 125V

## Features & Benefits

Auto-ground clip assures positive ground.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

One-piece brass triple-wipe power contacts for lasting retention.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Backed-out tri-drive steel terminal screws.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	1	Outlet Type	Commercial, Indoor
Application Sector	Residential/Commercial	Standard	UL 498, WC596
Type	Outlet		

### Dimensions

---

Product Width US	1.49 in	Product Depth US	1.0 in
------------------	---------	------------------	--------

---

Product Height US	1.49 in	Product Length US	2.0E-4 in
-------------------	---------	-------------------	-----------

---

### Listing Agencies / 3rd Party Agencies

---

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

---

### Technical Information

---

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

---

Voltage	125.0 V		
---------	---------	--	--

---