



Pass and Seymour
20A 125V Short Strap Spec Grade Single Receptacle, Side Wire, White
Part No. 5358W



Short Strap Spec Grade Single Receptacle, Side Wire, 20A 125V

Features & Benefits

Auto-ground clip assures positive ground.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

One-piece brass triple-wipe power contacts for lasting retention.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Backed-out tri-drive steel terminal screws.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007585834
Country Of Origin	Mexico	Number of Receptacles	1
Application Sector	Commercial	Standard	UL 498, WC596
Type	Outlet		

Dimensions

Product Width US	1.49 in	Product Depth US	1.0 in
Product Height US	1.49 in	Product Length US	2.0E-4 in
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	CSA File Number	16063
Technical Information			
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor