



Pass and Seymour
20A 125V Dual-Controlled Plug Load Duplex Receptacle, Black
Part No. 5362CDBK



Permanent controlled receptacle marking allows for long-lasting, easy identification of controlled receptacle for end-users. NEMA-approved and compliant with 2014 NEC, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.

Features & Benefits

- Can be wired to any number of system-based or stand-alone plug load control solutions.
 - .032 inch thick, brass, triple-wipe power contacts for lasting retention.
 - .032 inch thick, brass, triple-wipe power contacts for lasting retention.
 - Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
 - Impact-resistant nylon face.
 - 8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.
 - Tri-drive terminal and mounting screws.
 - Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|-------------------|------------------------------------------|-----------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Black |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Outlet Type | Commercial, Energy Saving On/Off, Indoor | Warranty Type | 1-Year Limited Warranty |
| Type | Outlet | | |

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 1.32 in | Product Depth US | 0.78 in |
|------------------|---------|------------------|---------|

Product Height US 2.635 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|----------------|--------|---------|---------|
| Indoor/Outdoor | Indoor | Voltage | 125.0 V |
|----------------|--------|---------|---------|
