



Heavy-Duty Spec Grade Single Receptacle, Side-Wire Right Angle Slots, 20A 125V.

Features & Benefits

Auto-ground clip assures positive ground.

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

Backed-out tri-drive steel terminal screws.

One-piece brass triple-wipe power contacts for lasting retention.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	5351W
Color	White	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	16063		

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	20 A	Number of Poles	Double Pole

Wire Size

14 - 10 AWG

Voltage

125.0 V

Environmental Conditions

Flammability: UL94 V2
