Quiktron

10FT Red Q-Series Patch Cords CAT5E Non-Booted

Part No. 560-130-010

Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.

Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

Specifications

General Info

Product Line	Quiktron	Color	Red
UPC Number	884815750806	Country Of Origin	Vietnam
Product Type	Patch Cord	Features	Standard Diameter
Application Sector	Commercial, Industrial		

Dimensions

Product Weight US	0.25 lb	Product Length US	10.0 FT
Cable Length	10 ft		

Additional Information

RoHS Compliant	Yes

Technical Information

Operating Temperature Min	-10 °C	Category Performance Application	Cat5e
Compatibility	RJ-45	Wire Gauge	24 AWG
Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 µ in Gold
Jacket Application	Riser Rated	Bend Radius	0.82 in
Shielded/Unshielded Cable	Unshielded	Termination Style	Pre-Terminated
Conductor Stranding	Stranded	Operating Temperature Max	60 °C
Cable Type	Non-Booted	Jacket Rating	CM Rated
Cable Diameter	0.205 in	Braid	Non-braided Wiring
Connector 2	RJ-45 Male	Connector 1	RJ-45 Male
Operating Temperature	-10°-60°C	Operating Humidity	0-90% RH (Non-Condensing)
Number of Strands	7	Conductor Material	Copper
Voltage	300.0 V	Storage Temperature	-40° - 60° C