



Pass and Seymour
Short Strap Spec Grade Single Receptacle, Side Wire, 15A, 250V, Ivory
Part No. 5658I



Short Strap Spec Grade Single Receptacle, Side-Wire, 15A 250V

Features & Benefits

Auto-ground clip assures positive ground.	Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.	Backed-out tri-drive steel terminal screws.
One-piece brass triple-wipe power contacts for lasting retention.	For covering patents, see www.legrand.us/patents .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 498, WC596		

Dimensions

Product Width US	1.49 in	Product Depth US	1.0 in
------------------	---------	------------------	--------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

Technical Information

Phase	3	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	250.0 V
