



Quiktron  
Q-Series Patch Cords, CAT6, Non-Booted, White, 6 FT  
Part No. 566-125-006



Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.

## Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

## Specifications

### General Info

Product Line	Quiktron	Color	White
UPC Number	884815783217	Country Of Origin	Vietnam
Features	Standard Diameter	Application Sector	Commercial, Industrial
Warranty Type	5-Year	Type	Copper Patch Cord

### Dimensions

Product Weight US	0.15 lb	Product Length US	6.0 FT
Cable Length	6 ft		

### Additional Information

RoHS Compliant	Yes
----------------	-----

### Technical Information

Jacket Material	PVC	Operating Temperature Min	-10 °C
Category Performance Rating	Cat6	Compatibility	RJ-45
Wire Gauge	24 AWG	Storage Humidity	0-90% RH (Non-Condensing)
Plating Specification	50 µ in Gold	Jacket Application	Riser Rated
Bend Radius	0.896 in	Shielded/Unshielded	Unshielded
Termination Style	Pre-Terminated	Conductor Stranding	Stranded
Operating Temperature Max	60 °C	Cable Type	Non-Booted
Jacket Rating	CM Rated	Cable Diameter	0.224 in
Braid	Non-braided Wiring	Connector 2	RJ-45 Male
Connector 1	RJ-45 Male	Operating Temperature	-10°-60°C
Operating Humidity	0-90% RH (Non-Condensing)	Conductor Material	Copper
Voltage	300.0 V	Storage Temperature	-40° - 60° C