



Quiktron
Q-Series Patch Cords, CAT6, Non-Booted, Orange, 75 FT
Part No. 566-140-075



Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.

Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

Specifications

General Info

Product Line	Quiktron	UPC Number	884815757560
Country Of Origin	Mexico	Application Sector	Commercial, Industrial
Type	Copper Patch Cord		

Dimensions

Product Weight US	1.875 lb	Product Length US	75.0 FT
-------------------	----------	-------------------	---------

Additional Information

RoHS Compliant	Yes
----------------	-----